



WATER TREATMENT PRODUCTS

January 1, 2006

| CATALOG # | DESCRIPTION | U/M | NOTES |
|--------------------------------------|--|-----|-------|
| | Please call for availability or lead time prior to placing your order. | | |
| 7600-111 (NEW #) 7600-101 (OLD #) | INCUMATE™, Incubation Controller, 110 Vac. Ship. Wt. 8# Ship. Dim. 9" x 9-1/2" x 16-1/2" | EA | |
| 7600-112 (NEW #) 7600-102 (OLD #) | INCUMATE™, Incubation Controller, 220 Vac. | EA | |
| 7780-100 | COLUMN FILTRATION SYSTEM, 4-Station Ship. Wt. Ship. Dim. Box 1 60# 15-1/2" x 47" x 19-1/2" Box 2 60# 15-1/2" x 47" x 19-1/2" Box 3 15# 3" x 5" x 50" | EA | |
| 7780-200 | COLUMN FILTRATION SYSTEM, 6-Station Ship. Wt. Ship. Dim. Box 1 70# 15-1/2" x 51" x 15-1/2" Box 2 70# 15-1/2" x 51" x 15-1/2" Box 3 15# 3" x 5" x 64" | EA | |
| | FLOC ILLUMINATORS FOR OLDER MODEL JARTESTERS ARE NON-STOCK/CUSTOM MANUFACTURED. | | |
| 7790-500/120 | FLOC ILLUMINATOR, 120 Vac., 50-60 Hz. f/ 7790-400, 6-Station Stirrer Ship.Wt. 20# Ship.Dim.42" x 12" x 8" | EA | |
| 7790-502/220-50 | FLOC ILLUMINATOR, 220 Vac., 50 Hz. f/ 7790-402, 6-Station Stirrer Ship.Wt. 20# Ship.Dim.42" x 12" x 8" | EA | |
| 7790-502/220-60 | FLOC ILLUMINATOR, 220 Vac., 60 Hz. f/ 7790-402, 6-Station Stirrer Ship.Wt. 20# Ship.Dim.42" x 12" x 8" | EA | |
| 7790-550/120 | FLOC ILLUMINATOR, 120 Vac., 50-60 Hz. f/ 7790-100, 4-Station Stirrer Ship.Wt. 15# Ship.Dim.30" x 12" x 7" | EA | |
| 7790-552/220-50 | FLOC ILLUMINATOR, 220 Vac., 50 Hz. f/ 7790-102, 4-Station Stirrer Ship.Wt. 15# Ship.Dim.30" x 12" x 7" | EA | |
| 7790-552/220-60 | FLOC ILLUMINATOR, 220 Vac., 60 Hz. f/ 7790-102, 4-Station Stirrer Ship.Wt. 15# Ship.Dim.30" x 12" x 7" | EA | |
| 7790-630 (NEW #) 7790-600 (OLD #) | B-KER2®, Complete, Square Lab Jars, 2-Liter Molded Acrylic w/ ball valve Bker Dim : 7-15/16" H x 4-15/16" W (ea.side) Ship.Wt. Ship.Dim. 1 (ea) 3# 13" x 7" x 6" 4 (ea) 10# 18" x 13" x 12" 6 (ea) 14# 18" x 13" x 12" | EA | |
| 7790-620 | BEAKERS, Round, Glass, 1000 ml | EA | |
| 7790-650 | DOSER BAR, 4 Place Ship. Wt. 5# Ship. Dim. 5-1/2" x 8-1/2" x 35" | EA | |
| 7790-660 | DOSER BAR, 6 Place Ship. Wt. 6# Ship. Dim. 5-1/2" x 8-1/2" x 47" | EA | |

**WATER TREATMENT PRODUCTS**

January 1, 2006

| CATALOG # | DESCRIPTION | U/M | NOTES |
|---|--|-----|-------|
| PB-700 Series Six-Paddle Standard JarTester | | | |
| <p>Each Six-Paddle Standard JarTester comes complete with built-in Anti-Glare Panel, Floc Illuminator, your choice of either Six Standard, Round, Glass, 1-Liter Laboratory Beakers or Six B-KER2® Square, Acrylic, 2-Liter Jar-Testing Jars, and a One-Year Manufacturer's Warranty.</p> | | | |
| 7790-701 | JAR TESTER, STANDARD, w/ Glass Beakers 120 Vac., 60 Hz. Ship.Wt. 70# Ship.Dim. 15 1/2 x 47 x 19 1/2 | EA | |
| 7790-702 | JAR TESTER, STANDARD, w/ Glass Beakers, 220 Vac., 50/60 Hz., CE Approved Ship.Wt. 70# Ship.Dim. 15 1/2 x 47 x 19 1/2 | EA | |
| 7790-711 | JAR TESTER, STANDARD, w/ Square Lab Jars 120 Vac., 60 Hz. Ship.Wt. 78# Ship.Dim. 15 1/2 x 47 x 19 1/2 | EA | |
| 7790-712 | JAR TESTER, STANDARD, w/ Square Lab Jars 220 Vac., 50/60 Hz., CE Approved Ship.Wt. 78# Ship.Dim. 15 1/2 x 47 x 19 1/2 | EA | |
| <p>Please call for availability or lead time prior to placing your order.</p> | | | |

**WATER TREATMENT PRODUCTS**

January 1, 2006

| CATALOG # | DESCRIPTION | U/M | NOTES |
|--|--|-----|-------|
| PB-750 Series Four-Paddle Standard JarTester | | | |
| <p>Each Four-Paddle Standard JarTester comes complete with built-in Anti-Glare Panel, Floc Illuminator, your choice of either Four Standard, Round, Glass, 1-Liter Laboratory Beakers or Four B-KER2® Square, Acrylic, 2-Liter Jar-Testing Jars, and a One-Year Manufacturer's Warranty.</p> | | | |
| 7790-751 | JAR TESTER, STANDARD, w/ Glass Beakers 120 Vac., 60 Hz. Ship.Wt. 55# Ship.Dim. 15 1/2 x 35 x 19 1/2 | EA | |
| 7790-752 | JAR TESTER, STANDARD, w/ Glass Beakers 220 Vac., 50/60 Hz., CE Approved Ship.Wt. 55# Ship.Dim. 15 1/2 x 35 x 19 1/2 | EA | |
| 7790-761 | JAR TESTER, STANDARD, w/ Square Lab Jars 120 Vac., 60 Hz. Ship.Wt. 63# Ship.Dim. 15 1/2 x 35 x 19 1/2 | EA | |
| 7790-762 | JAR TESTER, STANDARD, w/ Square Lab Jars 220 Vac., 50/60 Hz., CE Approved Ship.Wt. 63# Ship.Dim. 15 1/2 x 35 x 19 1/2 | EA | |
| Please call for availability or lead time prior to placing your order. | | | |



WATER TREATMENT PRODUCTS

January 1, 2006

| CATALOG # | DESCRIPTION | U/M | NOTES |
|--|--|-----|-------|
| PB-900 Series Six-Paddle Programmable JarTester | | | |
| <p>Each Six-Paddle Programmable JarTester comes complete with built-in Anti-Glare Panel, Floc Illuminator, your choice of either Six Standard, Round, Glass, 1-Liter Laboratory Beakers Six B-KER2® Square, Acrylic, 2-Liter Jar-Testing Jars, and a One-Year Manufacturer's Warranty.</p> | | | |
| 7790-901 | JAR TESTER, PROGRAMMABLE, w/ Glass Beakers 120 Vac., 60 Hz. Ship.Wt. 70# Ship.Dim. 15 1/2 x 47 x 19 1/2 | EA | |
| 7790-902 | JAR TESTER, PROGRAMMABLE, w/ Glass Beakers 220 Vac., 50/60 Hz. Ship.Wt. 70# Ship.Dim. 15 1/2 x 47 x 19 1/2 | EA | |
| 7790-911 | JAR TESTER, PROGRAMMABLE, w/ Square Lab Jars 120 Vac., 60 Hz. Ship.Wt. 78# Ship.Dim. 15 1/2 x 47 x 19 1/2 | EA | |
| 7790-912 | JAR TESTER, PROGRAMMABLE, w/ Square Lab Jars 220 Vac., 50/60 Hz. Ship.Wt. 78# Ship.Dim. 15 1/2 x 47 x 19 1/2 | EA | |
| <p>Please call for availability or lead time prior to placing your order.</p> | | | |



WATER TREATMENT PRODUCTS

January 1, 2006

| CATALOG # | DESCRIPTION | U/M | NOTES |
|---|--|-----|-------|
| PB-950 Series Four-Paddle Programmable JarTester | | | |
| <p>Each Four-Paddle Programmable JarTester comes complete with built-in Anti-Glare Panel, Floc Illuminator, your choice of either Four Standard, Round, Glass, 1-Liter Laboratory Beakers Four B-KER2® Square, Acrylic, 2-Liter Jar-Testing Jars, and a One-Year Manufacturer's Warranty.</p> | | | |
| 7790-951 | JAR TESTER, PROGRAMMABLE, w/ Glass Beakers 120 Vac., 60 Hz. Ship.Wt. 55# Ship.Dim. 15 1/2 x 35 x 19 1/2 | EA | |
| 7790-952 | JAR TESTER, PROGRAMMABLE, w/ Glass Beakers 220 Vac., 50/60 Hz. Ship.Wt. 55# Ship.Dim. 15 1/2 x 35 x 19 1/2 | EA | |
| 7790-961 | JAR TESTER, PROGRAMMABLE, w/ Square Lab Jars 120 Vac., 60 Hz. Ship.Wt. 63# Ship.Dim. 15 1/2 x 35 x 19 1/2 | EA | |
| 7790-962 | JAR TESTER, PROGRAMMABLE, w/ Square Lab Jars 220 Vac., 50/60 Hz. Ship.Wt. 63# Ship.Dim. 15 1/2 x 35 x 19 1/2 | EA | |
| PB-981 Two-Paddle Programmable JarTester | | | |
| <p>The Two-Paddle Programmable JarTester comes complete with built-in Anti-Glare Panel, Floc Illuminator, Two B-KER2® Square, Acrylic, 2-Liter Jar-Testing Jars, and a One-Year Manufacturer's Warranty.</p> | | | |
| 7790-981 | JAR TESTER, PROGRAMMABLE, w/ Square Lab Jars 120 Vac., 60 Hz. Ship.Wt. 41# Ship.Dim. 15 1/2 x 35 x 19 1/2 | EA | |
| Please call for availability or lead time prior to placing your order. | | | |

**WATER TREATMENT PRODUCTS**

January 1, 2006

| CATALOG # | DESCRIPTION | U/M | NOTES |
|-----------------|---|-----|-------|
| 7790-800/120 | STIRRER, SINGLE-PADDLE, Standard, Pole Mount (No Legs Or Frame, 300 RPM, 120Vac) | EA | |
| 7790-802/220 | STIRRER, SINGLE-PADDLE, Standard, Pole Mount (No Legs Or Frame, 300 RPM, 220Vac) | EA | |
| 7790-851 | MOTORBOX, SINGLE STATION, Stirrer, 120V w/Adapter, Standard Controller, (No Legs, Frame, or Paddle) | EA | |
| 7790-852 | MOTORBOX, SINGLE STATION, Stirrer, 220V w/Adapter, Standard Controller, (No Legs, Frame, or Paddle) | EA | |
| 7791-020 | CARRYING/SHIPPING CASE, (ATA 300) f/ 7790-750 & 950 Stirrer Family Ship.Wt. 30# (Empty) Ship.Dim. 36 1/2" x 13 1/2" x 19 1/2" | EA | |
| 7800-200 | CROWN PRESS™ BELT PRESS SIMULATOR Ship. Wt. 60# Ship.Dim. 32-1/2" x 16-1/2" x 21-1/2" | EA | |
| 8390-000 | GROUNDWATER SAMPLER, Stainless Steel 1-Liter Capacity | EA | |
| 8390-500 | GROUNDWATER SAMPLER, Stainless Steel .5-Liter Capacity | EA | |
| 8392-001 | SEWAGE SAMPLER, Dissolved Oxygen Ship.Wt. 11# Ship.Dim. 16 1/4" x 9 1/4" x 9" | EA | |
| 8392-301 | DIPPER SAMPLER, AC/DC, w/Timer, Stainless Steel Ship.Wt. 116# Ship.Dim. 24 1/4" x 16 1/8" x 32 1/8" | EA | |
| 8400-300 | MANIFOLD, 3-Stack Ship.Wt. 4# Ship.Dim. 13" x 8" x 7" | EA | |
| 8400-330 | MANIFOLD SYSTEM COMPLETE, 3-Stack, w/ Pump 120 Vac., 50/60 Hz. (2 Boxes) Ship.Wt. / Ship.Dim. 4# 13" x 8" x 7" 20# 17" x 13" x 13" | EA | |
| 8400-332/220-50 | MANIFOLD SYSTEM COMPLETE, 3-Stack, w/ Pump 220 Vac., 50 Hz. (2 Boxes) Ship.Wt. / Ship.Dim. 4# 13" x 8" x 7" 20# 17" x 13" x 13" | EA | |
| 8400-600 | MANIFOLD, 6-Stack Ship.Wt. 7# Ship.Dim. 23" x 10" x 10" | EA | |
| 8400-660 | MANIFOLD SYSTEM COMPLETE, 6-Stack, w/ Pump 120 Vac., 50/60 Hz. (2 Boxes) Ship.Wt. / Ship.Dim. 7# 23" x 10" x 10" 20# 17" x 13" x 13" | EA | |
| 8400-662/220-50 | MANIFOLD SYSTEM COMPLETE, 6-Stack, w/ Pump 220 Vac., 50 Hz. (2 Boxes) Ship.Wt. / Ship.Dim. 7# 23" x 10" x 10" 20# 17" x 13" x 13" | EA | |